

## Digital Thermo-Hygrometer T003

### 디지털 온습도계 T003 사용설명서

#### 각부 명칭



#### 제품특징

- 1) 보기편한 대형 LCD 표시부
- 2) 0.1°C 단위로 정밀한 온도 표시
- 3) C/F °C 표시
- 4) 패적 / 불쾌 지수 아이콘
- 5) 온습도 MAX/MIN 표시

#### 실내 온습도 측정

- 1) 제품 뒷면에 건전지 커버를 열고 절연 시트를 제거한 후 전원이 켜지는지 확인하십시오.
- 2) 제품을 안정된 장소에 설치하십시오.
- 3) 패적/불쾌 지수 아이콘 표시 가능

패적/불쾌	DISPLAY		아이콘
40~70%	20~25°C	55% RH	^^
~40%	0~50°C	34% RH	>>
70%~	0~50°C	75% RH	<<
40~70%	> 20~25°C <	75% RH	No Show

↑ 패적  
↓ 불쾌

#### 제품사양

품명 : 디지털 온습도계  
모델명 : T003  
사용온도 : 0 ~ 50°C (32~122°F)  
습도 : 20% ~ 95%(RH)  
규격(L x W x H) : 100 x 82 x 11mm  
제품전원 : CR2025 전지 1개

#### 건전지 교체 방법측정

1. 표시부의 숫자표시가 흐려졌을 경우 전지를 교체해 주세요.
  2. CR2025 1개를 준비하십시오.
  3. 제품 뒷면에 전지 커버를 열고 방전 된 전지를 빼내세요.
  4. +/- 표시에 맞춰 전지를 삽입하신 후 전지 커버를 닫아주세요.
  5. 전지 교체 후 온도와 습도를 재 측정하는 데는 약간의 시간이 소요됩니다.
  6. 사용이 끝난 전지는 어린이의 손에 닿지 않는 곳에 보관하시고, 장시간 사용하지 않을 때는 반드시 전지를 제품에서 분리하여 보관해 주세요.
- \*제품에 삽입되어 있는 전지는 작동 확인을 이므로, 전지 수명이 짧을 수 있습니다.

#### FEATURES

Temperature range: 0 - 50 °C ( 32- 122°F), resolution 0.1 °C/°F  
Humidity range: 20% - 99%  
Memory max/min temperature and humidity  
Comfort level display  
Powered by 1pcs CR2025 battery (Including)

#### OPERATION

----- MAX / MIN -----

Press "MAX/MIN" key once to view MAX temperature and humidity record.  
Press "MAX/MIN" key again to view MIN temperature and humidity record.

----- TEMPERATURE DISPLAY FORMAT -----

Press "C/F" key once to toggle the display between °C and °F.

CAS

카스고객지원센터 1577-5578